

Immersed learning

GENELEC MONITORS DELIVER FOR NEW TOKYO COLLEGE OF MUSIC CAMPUS





SMART ACTIVE MONITORING SOLUTION POWERS 5.1.2 CONFIGURATION AT NEW FLAGSHIP RECORDING STUDIO

s the oldest private music institute in Japan and staffed by a distinguished team of lecturers, Tokyo College of Music (TCM) is a prestigious destination for any aspiring student. TCM takes

its status very seriously and is constantly looking to develop and improve its facilities to ensure its students receive the best possible education. The latest example of this has

seen the creation of the new Nakameguro/ Daikanyama campus, which has been created to give its composition students access to even higher quality recording facilities. Genelec is at the heart of the new campus, providing monitoring solutions to a variety of spaces in both stereo and immersive formats.

While the campus features a variety of Genelec monitoring solutions, the highlight

THE STUDIO NEEDED TO BE CAPABLE OF RECORDING AN ENTIRE ORCHESTRA, AND SINCE WE HAVE A CONCERT HALL AND OTHER LARGE PERFORMANCE SPACES ON CAMPUS, WE WANTED THE STUDIO TO MAKE EFFICIENT USE OF THESE FACILITIES

can be found in the flagship recording studio. "The studio is used mainly by students who major in the Fine Art/Film Scoring course within the composition program," explains TCM lecturer Hideaki Sano. "The course focuses on composition, arrangement and performance, but also studies practical techniques related to pre-production, studio recording, producing, and so on. The studio needed to be capable of recording an entire orchestra, and since we have a concert hall and other large performance spaces on campus, we wanted the studio to make efficient use of these facilities."

With this brief in mind it was clear that the studio would need to be the centrepiece of the new campus. To ensure the best possible results, TCM turned to world-renowned

acoustician, Masami "Sam" Toyoshima, to handle the studio's acoustic design. Meanwhile, the equally important task of studio planning and operation was given to Mixer's Lab, thanks to its history and track record running its own studios as well as offering engineering and consultancy services.

With a 48-channel API Legacy AXS console taking pride of place in the mix position, the technology in the studio is clearly high-end, matching the standards that TCM demands. Nowhere is this clearer than with the studio monitoring. The solution comprises Genelec 1234A, 1238AC and 1238DF smart active main monitors in a 5.1.2 immersive configuration, with 8351A coaxial monitors for stereo nearfield monitoring.



A MONITOR NEEDS TO BE COMFORTABLE TO LISTEN TO, AND GENELEC HAS THAT QUALITY - PLUS THE ACCURACY TO COMPREHEND EVERY DETAIL OF THE SOUND WHATEVER THE GENRE

more 1238DFs as height speakers - due to For Hideo Takada of Mixer's Lab, the decision the compact nature of the studio." to go with Genelec monitors was an easy one: "I've been using Genelec reference monitors at work for a long time, so I know their sound For stereo nearfield work, TCM opted for inside out. They work well with acoustic 8351A three-way point source monitors from The Ones series. "What's great about instruments, pop music, and a wide variety of genres. It's a studio monitor you can trust." coaxial monitors is that you get one coherent If the choice of brand was an easy decision, sound," explains Mixer's Lab's Tatsuo Umezu. the configuration of the space was a different "A certain sound can be perceived from one matter entirely. "The college originally point as if it's a matter of course, and the requested the studio to be at least a 2-channel centre of the sound doesn't get 'blurred'. I can tell exactly where the mic was placed, and environment, and be able to conduct highhow far it was from the instrument. I suppose quality recording," recalls Takada. "But as the studio planning developed, we considered this is exactly what Genelec aimed for." that it should support surround. I had just experienced Dolby Atmos mixing myself, and Reflecting on the qualities the Genelec realised the importance of it, so we opted monitoring solutions have brought TCM, Sano for 1234As as L/R, a 1238AC for the centre is clearly very happy with their performance: channel, two 1238DFs for surrounds and two "Genelec monitors have the same sound even



when the playback volume is low, and that's one of the benefits. And the fact that it has become the industry standard is the key to our choice. Experiencing that industry standard sound is extremely beneficial for our students before they start to work as professionals.

"It's about the balance of the richness and the accuracy of the sound," he continues. "A monitor needs to be comfortable to listen to, and Genelec has that quality – plus the accuracy to comprehend every detail of the sound whatever the genre. Genelec can precisely playback an orchestra, a violin solo, pop music, EDM, and much more. It's a monitor we can completely count on."





EQUIPMENT LIST:

- 2 x 1234A
- 1 x 1238AC
- 4 x 1238DF
- 2 x 8351A

GENELEC OY OLVITIE 5 | 74100 | IISALMI, FINLAND | TEL. +358 17 83881 | ENQUIRIES@GENELEC.COM | WWW.GENELEC.COM

