

POSITAL

FRABA

RADIOGRAPHY AND FLUOROSCOPY SYSTEM



Machine Category:
X-Ray Apparatus

Industry: Medical Equipment

Country: China

Product Series:
IXARC UCD

Specification:
IXARC Magnetic rotary encoder, SSI + Incremental Output

Competing Technical Solution:
Replacement of Baumer encoder

Benefits of Technical Solution

The draw wire sensor is used in the X-Ray Stand Wall "XR656" to detect the vertical position and rotational angle. Patients can stand still and be X-rayed without repositioning.

Reasons for Choosing POSITAL

Proven Wiegand multiturn counting technology.
Good customer access based on existing business.
Short reaction time to customization specification request.

Author: Hongyu Yang
Hongyu.yang@posital.sg



GE Healthcare

Confidential! For internal use and training of authorized sales partners of POSITAL only.
Information may not be disclosed to third parties!

AMERICAS
FRABA Inc.
1800 East State Street, Suite 148
Hamilton, NJ 08609-2020, USA
T +1 609 750-8705
www.posital.com, info@posital.com

EUROPE
POSITAL GmbH
Zeppelinstrasse 2
Köln 50667, GERMANY
T +49 221 96213-0, F +49 221 96213-20
www.posital.eu, info@posital.eu

ASIA
FRABA Pte. Ltd.
30 Kallang Place, #04-16/17
Singapore 339159, SINGAPORE
T +65 6514 8880, F +65 6271 1792
www.posital.sg, info@posital.sg