

Normet Resin Capsule

REINFORCEMEN

ROCLOC® Resin Capsules

ROCK



RocLoc® Resin Capsules are a two-compartment capsule system that provides a quick and easy alternative to grout anchoring rock bolts. When mixed, the two components form a rapidly curing compound that binds the rock bolt to the surrounding strata, providing anchorage and corrosion protection. RocLoc® is permanent support used in combination with appropriate rock bolts and is suited for rock reinforcement in mining and tunneling construction projects.

WORKING PRINCIPLE

The resin capsules contain two components separated by a thin membrane. One compartment contains the resin mastic, and the other compartment contains the catalyst paste.

The capsule is placed into a pre-drilled borehole, followed by the insertion of the rock bolt.

The insertion and rotation of the rock bolt breaks the sheath, allowing the resin and catalyst to mix. This thixotropic compound sets after a specified setting time and creates a chemical bond between the anchor and the strata.

BENEFITS

- > Resin capsules are suitable for soft, fractured and hard rock.
- Immediate bonding of the bolt to surrounding strata, allows for immediate reinforcement and rapid advancement of support.
- Rapid strength development allows for support to become safe and active shortly after installation.
- > Thixotropic compound allows for overhead installations.
- > Can be used for end-anchorage or full-length anchorage and load distribution.
- > Full encapsulation provides additional corrosion protection
- Individual capsules are provided with identification and subject to end-to-end testing for quality control

RANGE AND SPECIFICATIONS

Strength Specifications

Requirements:		
Standard	19 MPa	
High Strength	23 MPa	

Set Times Specifications

_	oct i mico opcomodatorio				
	Set Time	Standard Colour Code	Spin Time*	Hold Time*	
	15 sec	Purple	7 sec	8 sec	
	20 sec	Black	8 sec	12 sec	
	30 sec	Red	10 sec	20 sec	
	60 sec	Green	15 sec	45 sec	
	120 sec	Blue	20 sec	100 sec	
	5/10 min	Yellow	20 sec	10 mins	

^{*} spin time and hold times established at 20 degrees C. Set time will be faster(slower) when the temperature is higher(lower).

Strength Specifications

Particulars	Value (in mm)
Standard Diameters	23, 25, 28, 30, 32, 35
Standard Lengths	350, 400, 450, 500, 600, 700, 900, 1000, 1100, 1150, 1350

 $^{^{\}star}\, other\, dimensions\, can\, be\, manufactured\, if\, required$







