



flow, stop and go®



NEOPERL® PERLATOR® HC FLOW THRU AERATORS

STD size, aerated & flow-thru streams

Models with restrictor

Color code	Flow rate	STD insert	Female M22×1	Male M24×1
●	√ optimal performance and aeration from 0.2 to 1 bar	<u>025107000</u>	<u>015809000</u>	<u>015810000</u>

PCA® models

Color code	Flow rate	STD insert	Female M22×1	Male M24×1
●	5.0 l/min	<u>025115100</u>	<u>015833000</u>	<u>015815000</u>
●	6.0 l/min	<u>025112100</u>	<u>015830000</u>	<u>015812000</u>
●	2.2 gpm max.	<u>025113100</u>	<u>015831000</u>	<u>015813000</u>
○	8.0 l/min	<u>025114100</u>	<u>015832000</u>	<u>015814000</u>



Aerated stream via the outer stream path (left) and stream for filtered water through the inner path (right)