



flow, stop and go®



# NEOPERL® TENMILL AERATORS

## All sizes, aerated stream

### Models with restrictor

Flow rate	Insert (10 mm)	Male M13.5×1
Low flow (1.1 - 1.6 l/min)	<u>022500000</u>	<u>012500000</u>
Medium flow (1.7 - 2.1 l/min)	<u>022501000</u>	<u>012501000</u>

### PCA® models

Color code	Flow rate	Insert (10 mm)	Male M13.5×1
●	0.35 gpm (1.9l/min) max.		<u>012504000</u>
●	0.5 gpm (1.3 l/min) max.	<u>022505000</u>	<u>012505000</u>



flow, stop and go®



# NEOPERL® TENMILL AERATORS

## All sizes, laminar stream

### Models with restrictor

Flow rate	Insert (10 mm)	Male M13.5×1
1.9 l/min (0.5 gpm)		<u>012511000</u>