

Compatibility chart

Adapter for dental hollow body instruments

Instrument type: Air scaler handpiece

| Manufacturer | Instrument name | Adapter Careclave Carebox Blue | Adapter MELAtherm |
|--------------|----------------------|--------------------------------|----------------------|
| KaVo | SONICflex 2003 | ME02601 | ME80660 |
| KaVo | SONICflex quick 2008 | ME02601 | ME80660 |
| KaVo | Sonicflex 2000 | ME02601 | ME80660 |
| NSK | Ti-MAX S950 / S970 | see turbines, page 5 | see turbines, page 5 |
| NSK | AS2000 M4 | ME02609 | ME73904 |
| Sirona | SIROAIR handpiece | see turbines, page 5 | see turbines, page 5 |
| W&H | Proxeo/Synea | see turbines, page 5 | see turbines, page 5 |
| Others | - | see turbines, page 5 | see turbines, page 5 |

Instrument type: Piezo handpiece

| Manufacturer | Instrument name | Adapter Careclave Carebox Green | Adapter MELAtherm |
|------------------|---|---------------------------------|-------------------|
| Acteon (Satelec) | Newtron / Suprasson | ME80757 | ME80757 |
| DTE | D600 | ME80757 | ME80757 |
| DTE | Prophy+ | ME80757 | ME80757 |
| EMS | Piezon / Piezon LED | ME80790 | ME80790 |
| Dürr | MyLunos | ME80790 | ME80790 |
| KaVo | PiezoLED / PIEZOsoft ultrasonic Scaler | ME80753 | ME80753 |
| KaVo | Sonosoft / Piezo LUX | ME80790 | ME80790 |
| Coming soon | KaVo eSCALER | ME12411 | ME12411 |
| Mectron | Multipiezo/Piezo Smart/Micropiezo/Compact Piezo | ME80790 | ME80790 |
| NSK | Varios (Satelec) | ME80757 | ME80757 |
| Sirona | Siroson / Sirosonic / PerioSonic | ME80771 | ME80771 |

Instrument type: Piezo handpiece

| Manufacturer | Instrument name | Adapter Careclave Carebox Green | Adapter MELAtherm |
|--------------|---|---------------------------------|-------------------|
| Woodpecker | Prophy+ without specification A/S | ME80790 | ME80790 |
| Woodpecker | Prophy+ with A/S specification | ME80757 | ME80757 |
| Woodpecker | Prophy+ „gold“ | ME80757 | ME80757 |
| W&H | Tigon/Tigon+/Pyon 2/Proxeo Ultra/Piezomed | ME80790 | ME80790 |

Instrument type: Air polishing handpiece

| Manufacturer | Instrument name | Adapter Careclave Carebox Green | Adapter MELAtherm |
|--------------|--|---------------------------------|----------------------|
| EMS | AIR-FLOW (Prophylaxis Master) MAX / MAX 2.0 EL-308, PERIOFLOW EL-354 | ME80614 | ME80614 |
| EMS | AIR-FLOW Handy 3.0 EL-540, PERIOFLOW EL-542, PERIO Plus EL-545 | ME80613 | ME80613 |
| KaVo | RONDOflex plus 360 | - | see turbines, page 5 |
| KaVo | PROPHYflex 4 | - | see turbines, page 5 |
| Woodpecker | Prophy+ | ME80614 | ME80614 |
| Others | - | - | ME73904 |

Instrument type: Scaler tips

| Manufacturer | Instrument name | Adapter Careclave Carebox Green* | Adapter MELAtherm |
|------------------|-----------------------------------|----------------------------------|-------------------|
| Acteon (Satelec) | Newtron/Suprasson | ME80756 | ME80756 |
| Acteon (Satelec) | Piezotome Surgery 1. Gen & 2. Gen | - | ME80260 |
| Anthos | u-PZ6/u-PZ7 | ME80750 | ME80750 |
| Anthos | u-PZ6 S/u-PZ7 S | ME80756 | ME80756 |
| Castellini | Piezosteril 6/Piezolight 6 | ME80750 | ME80750 |
| Castellini | Piezosteril 6 S/Piezolight 6 S | ME80756 | ME80756 |
| DTE | D600 | ME80756 | ME80756 |
| DTE | Prophy+ | ME80756 | ME80756 |

Instrument type: Scaler tips

| Manufacturer | Instrument name | Adapter Careclave Carebox Green* | Adapter MELAtherm |
|--------------|---|----------------------------------|-------------------|
| Dürr | MyLunos | ME80750 | ME80750 |
| Dürr | Vector Scaler | ME80760 | ME80760 |
| EMS | Piezon/Piezon LED | ME80750 | ME80750 |
| EMS | Piezon Surgery | - | ME80260 |
| Hu-Friedy | Piezo E-Serie (EMS) | ME80750 | ME80750 |
| Hu-Friedy | Piezo S-Serie (NSK, Satelec, Hu-Friedy) | ME80756 | ME80756 |
| KaVo | SONOsoft, Piezo LUX | ME80750 | ME80750 |
| KaVo | SONICflex quick 2008 | ME80751 | ME80751 |
| KaVo | PIEZOsoft/PiezoLED | ME80752 | ME80752 |
| KaVo | SONICflex 2000/SONICflex 2003 | ME80790 | ME80790 |
| Komet | PiezoLine EM1, KA1, KA2 | ME80750 | ME80750 |
| Komet | PiezoLine SI1 | ME80760 | ME80760 |
| Komet | PiezoLine SF1LM | ME80790 | ME80790 |
| Mectron | Multipiezo/Piezo Smart/Micropiezo/Compact Piezo | ME80750 | ME80750 |
| Mectron | Piezosurgery | - | ME80260 |
| Morita | Solfy/Solfy LED | ME80760 | ME80760 |
| Morita | AirSolfy | ME80790 | ME80790 |
| NSK | Varios | ME80756 | ME80756 |
| NSK | Ti-Max S970/AS2000 | ME80790 | ME80790 |
| NSK | VarioSurg3 LED | - | ME80260 |
| Planmeca | LM-ProPower | ME80755 | ME80755 |
| Sirona | SIROSON/SIROSONIC/PerioSonic | ME80760 | ME80760 |
| Sirona | SIROAIR L | ME80790 | ME80790 |
| Stern Weber | SC-A2/SC-A3 | ME80750 | ME80750 |
| Stern Weber | SC-A2 S/SC-A3 S | ME80756 | ME80756 |

*If up to 6 torque wrenches with a diameter larger than 38 mm are to be prepared in the Carebox Green, the adapter M8 x 1, eccentric ME22407 is required.

Instrument type: Scaler tips

| Manufacturer | Instrument name | Adapter Careclave Carebox Green* | Adapter MELAtherm |
|--------------|---|----------------------------------|-------------------|
| Ultradent | Newtron | ME80756 | ME80756 |
| Woodpecker | Prophy+ without specification A/S | ME80750 | ME80750 |
| Woodpecker | Prophy+ with A/S specification | ME80756 | ME80756 |
| Woodpecker | Prophy+ „gold“ | ME80756 | ME80756 |
| W&H | Tigon/Tigon+/Pyon 2/Proxeo Ultra/Piezomed | ME80750 | ME80750 |
| W&H | Proxeo/Synea | ME80790 | ME80790 |

Instrument type: Handpieces and contra angles

| Manufacturer | Instrument name | Adapter Careclave Carebox Blue | Adapter MELAtherm |
|--------------|--|--------------------------------|-------------------|
| Bien-Air | NOVA/CA/PMP Prophy/CAP | ME02607 | ME80610 |
| Bien-Air | Contra angle heads | ME02606 | ME80630 |
| KaVo | MASTERmatic/EXPERTmatic/SMARTmatic/ SURGmatic/ENDOadvance | ME02607 | ME80610 |
| KaVo | COMFORTdrive | - | ME73904 |
| KaVo | Contra angle heads | ME02606 | ME80630 |
| W&H | Synea/Synea Short/Alegra | ME02607 | ME80610 |
| Morita | TorqTech | ME02607 | ME80610 |
| NSK | Chirurgie Contra angles/Ti-Max Z/Ti-Max X450/S-Max M/FXm Series/EX Serie/Ti-Max Z45L/nano Serie | ME02607 | ME80610 |
| Sirona | T1 Classic (Only classic) | ME02604 | ME80620 |
| Sirona | T1 Line/T2 Line/T2 S-Line | ME02607 | ME80610 |
| Others | Instrument with ISO coupling | ME02607 | ME80610 |
| Others | External spray channels | ME21914 | ME74135 |

Instrument type: Turbines (Note: Please select the turbine adapter according to the coupling on your dental unit).

| Coupling system | Adapter Careclave Carebox Blue | Adapter MELAtherm |
|-----------------|--------------------------------|-------------------|
| Bien-Air | ME02608 | ME73904 |
| KaVo MULTIflex | ME02601 | ME80660 |
| Midwest | ME02609 | ME73904 |
| NSK-Phatelus | ME02611 | ME80612 |
| Sirona-Turbine | ME02602 | ME80650 |
| W&H Roto Quick | ME02605 | ME80640 |
| Others | - | ME73904 |



Multifunctional cannula

| | Hersteller | Instrumentenbezeichnung | Adapter Careclave Carebox Green | Adapter MELAtherm |
|--------------------|------------|---|---------------------------------|-------------------|
| NEW | KaVo | Multifunctional cannula MF / 3F | ME80803 | ME80803 |
| Coming soon | Sirona | Multifunctional cannula Sirona Sprayvit | ME80802 | ME80802 |

For multifunctional cannulas, the ME73904 universal adapter can generally be used in the MELAtherm 10. Adapter solutions may be available from the instrument manufacturers. However, please check beforehand that the instruments are approved for machine reprocessing.

All information is provided without guarantee. The overview only shows physical connectivity. Always follow the reprocessing recommendations of the instrument manufacturers.